



LL3-DH05

Fiber-optic cables

FIBER-OPTIC SENSORS

SICK
Sensor Intelligence.



Ordering information

Type	part no.
LL3-DH05	5326021

Other models and accessories → www.sick.com/Fiber-optic_cables

Detailed technical data

Features

Device type	Fiber-optic cables
Functional principle	Proximity system
Fiber-optic head design	Threaded sleeve, Long end sleeve, Bendable sleeve, 90° deflection
Application	Heat-resistant (≥100°C)
Compatible fiber-optic amplifiers	GLL70, WLL80, WLL180, GLL170(T)
Sensing range max.	1,260 mm (Sensing range of WLL80 at 8 ms)
Minimal object diameter	0.02 mm ¹⁾
Optical fiber head	
Angle of dispersion	60°
Integrated lens	No
Compatibility tip adapters	No
Optical fiber	
Compatibility with infrared light	Yes ²⁾
Adapter end sleeves required	No
Included with delivery	Mounting, 2 x M4 hexagon nut, 1 x washer

¹⁾ Minimum detectable object was determined at optimum measuring distance and optimum setting.

²⁾ Reduced sensing ranges possible when using a fiber-optic amplifier with infrared light.

Mechanics

Optical fiber head	
Light emission	Axial
Thread diameter (housing)	M4
Optical fiber taper diameter	≥ 2.1 mm
Optical fiber taper length after 2 mm	≥ 90 mm
Minimum bend radius of end sleeve	10 mm
Optical fiber	
Fiber length	1,000 mm
Bending radius	25 mm
Dynamic flexibility (robotics)	No
Outside diameter, optical fiber cable connection	2.2 mm
Fiber arrangement	Multi-fiber
Core structure	S: 380 x Ø 0,5 µm R: 380 x Ø 0,5 µm Multi-fiber
Material	

Optical fiber head	Copper-zinc alloy (CuZn)
Sheath	Stainless steel
Fibers	Glass
Weight	90 g

Ambient data

Ambient operating temperature	-30 °C ... +350 °C
--------------------------------------	--------------------

Sensing ranges with GLL70

Operating mode 50 µs	165 mm
Operating mode 250 µs	410 mm
Operating mode 1 ms	570 mm
Operating mode 4 ms	950 mm

Sensing ranges with WLL80

Operating mode 16 µs	120 mm
Operating mode 70 µs	300 mm
Operating mode 250 µs	520 mm
Operating mode 500 µs	600 mm
Operating mode 1 ms	700 mm
Operating mode 2 ms	1,050 mm
Operating mode 8 ms	1,260 mm
Note	Sensing ranges related to fiber-optic sensors with type of light: visible red light

Sensing ranges with WLL180T

Operating mode 16 µs	55 mm
Operating mode 70 µs	220 mm
Operating mode 250 µs	580 mm
Operating mode 2 ms	1,170 mm
Operating mode 8 ms	1,240 mm
Note	Sensing ranges related to fiber-optic sensors with type of light: visible red light

Sensing ranges with GLL170

Operating mode 250 µs	290 mm
------------------------------	--------

Sensing ranges with GLL170T


Operating mode 50 µs	140 mm
Operating mode 250 µs	420 mm

Classifications

ECLASS 5.0	27270905
ECLASS 5.1.4	27270905
ECLASS 6.0	27270905
ECLASS 6.2	27270905
ECLASS 7.0	27270905
ECLASS 8.0	27270905

ECLASS 8.1	27270905
ECLASS 9.0	27270905
ECLASS 10.0	27270905
ECLASS 11.0	27270905
ECLASS 12.0	27270905
ETIM 5.0	EC002651
ETIM 6.0	EC002651
ETIM 7.0	EC002651
ETIM 8.0	EC002651
UNSPSC 16.0901	39121528

Dimensional drawing LL3-DH05



Dimensions in mm (inch)

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com